


Multilayer Chip Directional Couplers For W-CDMA


Conformity to RoHS Directive

HHM Series HHM2910E8

SHAPES AND DIMENSIONS



RECOMMENDED PC BOARD PATTERNS



ELECTRICAL CHARACTERISTICS

Frequency range	1700 to 1850MHz	1850 to 2000MHz
Coupling factor	20.9±1.0dB	20.2±1.0dB
Insertion loss	0.22dB max.*1 0.25dB max.*2	0.22dB max.*1 0.25dB max.*2
Isolation	34dB min.	34dB min.
VSWR	1.4max.	1.4max.
Power capacity	3W max.	3W max.
Temperature range	Operating Storage	Operating Storage
	−40 to +85°C	−40 to +85°C
	−40 to +85°C	−40 to +85°C

*1 25°C


*2 Operating temperature

• Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.


• All specifications are subject to change without notice.

FREQUENCY CHARACTERISTICS


COUPLING



ISOLATION & DIRECTIVITY



INSERTION LOSS



VSWR

