

RWS1000B/ME

A273-01-01/ME-A

SPECIFICATIONS (1/2)


ITEMS		MODEL	RWS1000B-12 /ME	RWS1000B-15 /ME	RWS1000B-24 /ME	RWS1000B-36 /ME	RWS1000B-48 /ME	
1	Nominal Output Voltage	V	12	15	24	36	48	
2	Maximum Output Current	A	84	67	42	28	21	
3	Maximum Output Power	W	1008	1005	1008	1008	1008	
4	Efficiency (Typ) (*13)	100/115VAC	% 81/82	% 81/82	% 84/85	% 84/85	% 83/85	
		200/230VAC	% 85/85	% 85/85	% 88/88	% 88/88	% 87/88	
5	Input Voltage Range	(*2)(*11)	-					85 - 265VAC (47 - 63Hz) or 120 - 340VDC
6	Input Current (Typ) (*13)	100/115VAC	A					13 / 11
		200/230VAC	A					7 / 5.5
7	Inrush Current (Typ)	(*1)(*3)	-					20A / 40A at 1st Inrush , 60A / 60A at 2nd Inrush
8	PFHC		-					Designed to meet IEC61000-3-2
9	Power Factor (Typ)	(*1)	-					0.98/0.95
10	Output Voltage Range		V 10.2 - 13.8	V 12.8 - 17.2	V 20.4 - 28.8	V 30.6 - 41.4	V 40.8 - 52.8	
11	Maximum Ripple & Noise (*4)	0≤Ta≤60°C	mV 150	mV 150	mV 180	mV 250	mV 300	
		-20≤Ta<0°C	mV 180	mV 180	mV 200	mV 300	mV 400	
12	Maximum Line Regulation	(*5)(*11)	mV 48	mV 60	mV 96	mV 144	mV 192	
13	Maximum Load Regulation	(*6)(*11)	mV 96	mV 120	mV 144	mV 216	mV 288	
14	Temperature Coefficient		-					Less than 0.02% / °C
15	Over Current Protection	(*7)	A 88.2 -	A 70.4 -	A 44.1 -	A 29.4 -	A 22.1 -	
16	Over Voltage Protection	(*8)	V 14.4 - 17.4	V 18.0 - 21.8	V 30.0 - 36.0	V 43.2 - 52.2	V 55.2 - 60.0	
17	Hold-up Time (Typ)	(*1)	-					20ms
18	Leakage Current	(*9)	-					Less than 0.3mA
19	Remote Sensing	(*14)	-					Possible
20	Monitoring Signal		-					-
21	Remote Control		-					-
22	Parallel Operation		-					-
23	Series Operation	(*14)	-					Possible
24	Operating Temperature	(*10)(*11)	-					-20 - +60°C (-20 - +50°C:100%, +60°C:60%)
25	Operating Humidity		-					20 - 90%RH (No Condensing)
26	Storage Temperature		-					-30 - +75°C
27	Storage Humidity		-					10 - 90%RH (No Condensing)
28	Cooling		-					Forced Air Cooling
29	Withstand Voltage		-					Input-FG : 2kVAC (20mA) 1xMOPP, Input-Output : 4kVAC (20mA) 2xMOPP, Output-FG : 1.5kVAC (20mA) 1xMOPP for 1min
30	Isolation Resistance		-					More than 100MΩ at 25°C and 70%RH Output to Chassis : 500VDC
31	Vibration		-					At no operating, 10 - 55Hz (Sweep for 1min) 19.6m/s ² Constant, X,Y,Z 1hour each.
32	Shock		-					Less than 196m/s ²
33	Safety		-					Approved by ES60601-1 3rd Edition, EN60601-1 3rd Edition, CSA-C22.2 No.60601-1 3rd Edition.
34	Line DIP		-					Designed to meet SEMI-F47 (200VAC Line only)
35	Conducted Emission	(*12)	-					Designed to meet EN55011/EN55032-A, FCC-A, VCCI-A
36	Radiated Emission	(*12)	-					Designed to meet EN55011/EN55032-A, FCC-A, VCCI-A
37	Immunity	(*12)	-					Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11
38	Weight (Typ)		g					2000
39	Size (W x H x D)		mm					127 x 63 x 198 (Refer to Outline Drawing)

*Read instruction manual carefully, before using the power supply unit.

=NOTES=

- *1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- *2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 - 240VAC(50-60Hz).
- *3. Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- *4. Please refer to Fig. A for measurement of Vo, line & load regulation and ripple voltage.
- *5. 85 - 265VAC, constant load.
- *6. No load-Full load, constant input voltage.
- *7. Constant current limit with automatic recovery. Over current condition for more than 5 seconds will cause the output to shut down. Avoid to operate at over load or short circuit condition.
- *8. OVP circuit will shut down output, manual reset (Re power on).
- *9. Measured by the each measuring method of UL, CSA, EN and Den-an(at 60Hz), Ta=25°C.
- *10. Output Derating
 - Refer to LOAD vs. AMBIENT TEMPERATURE(A273-01-02_).
 - Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.
- *11. Output derating needed when input voltage less than 90VAC. Refer to LOAD vs. INPUT VOLTAGE(A273-01-02_).
- *12. The power supply is considered a component which will be installed into a final equipment. The final equipment should be re-evaluated that it meets EMC directives.
- *13. Ta=25°C, nominal output voltage and maximum output power.
- *14. Refer to instruction manual(A273-04-01_).

Fig.A



C1 : Film Cap. 0.1μF
 C2 : Elect. Cap. 47μF