

**ZWS240BP/L**

SPECIFICATIONS


A253-01-01/L-B

ITEMS		MODEL	ZWS240BP -24/L	ZWS240BP -36/L	ZWS240BP -48/L	
1	Nominal Output Voltage	V	24	36	48	
2	Average Output Current	A	10	6.7	5.0	
3	Peak Output Current (*1)	A	20.0	13.4	10.0	
4	Average Output Power	W	240.0	241.2	240.0	
5	Peak Output Power (*1)	W	480.0	482.4	480.0	
6	Efficiency (Typ)	100VAC	%			
		(*2) 200VAC	%			
7	Input Voltage Range (*3)(*13)	-	85 - 265VAC (47 - 63Hz) or 120 - 370VDC			
8	Input Current (Typ) (*2)	A	2.8/1.5			
9	Inrush Current (Typ) (*2)(*4)	-	15A at 100VAC, 30A at 200VAC, Ta=25°C, Cold Start			
10	PFHC	-	Designed to meet IEC61000-3-2			
11	Power Factor (Typ) (*2)	-	0.98/0.93			
12	Output Voltage Range	V	21.6 - 27.5	32.4 - 39.6	39.6 - 52.8	
13	Maximum Ripple & Noise (*5)	0≤Ta≤70°C	mV	240	360	480
		-10≤Ta<0°C	mV	360	540	720
14	Maximum Line Regulation (*5)(*6)	mV	96	144	192	
15	Maximum Load Regulation (*5)(*7)	mV	192	288	384	
16	Temperature Coefficient (*5)	-	Less than 0.02% / °C			
17	Over Current Protection (*8)	A	20.10 -	13.47 -	10.05 -	
18	Over Voltage Protection (*9)	V	28.8 - 33.6	41.4 - 48.6	55.2 - 64.8	
19	Hold-up Time (Typ) (*2)	-	20ms			
20	Leakage Current (*10)	-	Less than 0.5mA. 0.2mA(Typ) at 100VAC / 0.4mA(Typ) at 230VAC			
21	Parallel Operation	-	-			
22	Series Operation	-	Possible			
23	Operating Temperature (*11)	-	Convection : -10 - +70°C (-10 - +50°C:100%, +60°C:65%, +70°C:30%)			
24	Operating Humidity	-	30 - 90%RH (No Condensing)			
25	Storage Temperature	-	-30 - +75°C			
26	Storage Humidity	-	10 - 90%RH (No Condensing)			
27	Cooling	-	Convection Cooling			
28	Withstand Voltage	-	Input - FG : 2kVAC (10mA), Input - Output : 3kVAC (10mA) Output - FG : 500VAC (20mA) for 1min			
29	Isolation Resistance	-	More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC			
30	Vibration	-	At no operating, 10 - 55Hz (Sweep for 1min) 19.6m/s <sup>2</sup> Constant, X,Y,Z 1hour each.			
31	Shock	-	Less than 196.1m/s <sup>2</sup>			
32	Safety	-	Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CSA60950-1, EN60950-1 (Expire date of 60950-1 : 20/12/2020), EN50178(OV II) Designed to meet DENAN at 100VAC Only.			
33	Conducted Emission (*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B			
34	Radiated Emission (*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B			
35	Immunity	-	Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11			
36	Weight (Typ)	g	720			
37	Size (W x H x D)	mm	95 x 53 x 212 ( Refer to Outline Drawing )			

\*Read instruction manual carefully, before using the power supply unit.

=NOTES=

- \*1. Operating time at peak output is less than 5sec, duty is less than 40%. For details, refer to peak output condition (A253-01-03\_).  
When the peak output more than 5 sec is continued, the output is shut down, manual reset.
- \*2. At 100VAC/200VAC, Ta=25°C, nominal output voltage and average output power.
- \*3. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 - 240VAC (50-60Hz).
- \*4. Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- \*5. Please refer to Fig. A for measurement of Vo, line & load regulation and ripple voltage.
- \*6. 90 - 265VAC, constant load.
- \*7. No load-Average load, constant input voltage.
- \*8. Constant current limit with automatic recovery. Avoid to operate at over load or short circuit condition.
- \*9. OVP circuit will shut down output, manual reset (Re power on).
- \*10. Measured by the each measuring method of UL, CSA, EN and DENAN (at 60Hz), Ta=25°C.
- \*11. Output Derating - Derating at standard mounting. Refer to output derating curve (A253-01-02\_).  
- When forced air cooling, refer to forced air cooling specifications (A253-01-04\_ , A253-01-05/L\_ , A253-01-06\_).  
- Load (%) is percent of average output power or average output current, do not exceed its derating of average load.
- \*12. At Ta=25°C and average output power.
- \*13. Output derating needed when input voltage less than 90VAC. Refer to output derating vs. input voltage (A253-01-02\_).



**ZWS240BP/L**

SPECIFICATIONS (FORCED AIR COOLING)

A253-01-05/L-A

ITEMS		MODEL	ZWS240BP -24/L	ZWS240BP -36/L	ZWS240BP -48/L
1	Nominal Output Voltage	V	24	36	48
2	Average Output Current	A	12.5	8.4	6.3
3	Peak Output Current (*1)	A	20.0	13.4	10.0
4	Average Output Power	W	300.0	302.4	302.4
5	Peak Output Power (*1)	W	480.0	482.4	480.0
6	Efficiency (Typ)	100VAC	%		
		(*)200VAC	%		
7	Input Voltage Range (*3)(*4)	-	85 - 265VAC (47 - 63Hz) or 120 - 370VDC		
8	Input Current (Typ) (*5)	A	3.6/1.8		
9	Hold-up Time (Typ) (*5)	-	16ms(typ) at 100VAC & Rated O/P Power, 20ms(typ) at 100VAC & 75% Load		
10	Operating Temperature (*6)	-	-10 - +70°C (-10 - +60°C:100%, +70°C:70%)		
11	Cooling (*7)	-	Forced Air Cooling		
12	Conducted Emission (*8)	-	Designed to meet EN55011/EN55032-A, FCC-A, VCCI-A		
13	Radiated Emission (*8)	-	Designed to meet EN55011/EN55032-A, FCC-A, VCCI-A		

\*Read instruction manual carefully, before using the power supply unit.

\*For other specification items, refer to specifications(A253-01-01/L- ).

=NOTES=

- \*1. Operating time at peak output is less than 5sec, duty is less than 40%. For details, refer to peak output condition (A253-01-03 ).  
When the peak output more than 5 sec is continued, the output is shut down, manual reset.
- \*2. At 100VAC/200VAC, Ta=25°C, nominal output voltage and average output power.
- \*3. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 - 240VAC (50-60Hz).
- \*4. Output derating needed when input voltage less than 90VAC. Refer to output derating vs. input voltage (A253-01-02 ).
- \*5. At 100VAC/200VAC, Ta=25°C, nominal output voltage and average output power.
- \*6. Output Derating - Derating at standard mounting. Refer to output derating curve (A253-01-06 ).  
- Load (%) is percent of average output power or average output current, do not exceed its derating of average load.
- \*7. Forced air cooling with air velocity more than 1.5m/s (measured at component side of PCB, air must flow through component side)
- \*8. At Ta=25°C and average output power.