
会TDK

Testing GBDriver RS3 Global Static Wear Levelling Effectiveness


0								0				
	GBDRIVER RS3 (SATA SSD Controller)											
RELATED	CAG3B Series (1.0" SATA 3Gbps CFastTM SSD, SDG3B Series (2.5" SATA 3Gbps SSD)											
PRODUCTS	SMG3B Series (SATA 3Gbps mSATA Flash Module)											
TESTED DATE	2011/12/1 16:00 ~ 2012/1/24 11:30											
TESTED BY	TDK Corp, Flash Memory Applied Business, ESS BU [K. TAKUBO]											
TEST PROCEDURE	(1) Loaded DOS in [16] Gbit Flash to occupy [90%] of all memory blocks.											
	(2) Executed repeated data writes to the REST [10%] blocks; data size:[128KByte].											
	(3) Log	ged S.M.	A.R.T. dat	a peridica	lly.							
SAMPLES	[5] Samples [NAND:					oo ∑	CONTROLLER: TDK GBDRIVER RS3					
	(WEEKLY						(WEEKLY CODE: 1011W3BHH)					
	[5] Samples [NAND:						CONTROLLER: TDK GBDRIVER RS3					
	(WEEKLY						(WEEKLY CODE: 1030LU602)					
] Samples NAND:						CONTROLLER:					
	(WEEKLY CODE:)											
RESULTS	PASS						·					
Erased Times	1,000	<u>2,000</u>	<u>3,000</u>	<u>4,000</u>	<u>5,000</u>	<u>6,000</u>	<u>7,000</u>	<u>8,000</u>	<u>9,000</u>	<u>10,000</u>		
Minimum	963	1,984	3,107	3,995	4,882	5,882		7,927	8,997	9,887		
Maximum	1,028	2,131	3,275	4,067	5,115	·		8,183	+	10,032		
_%	6.50%	7.35%		1.80%	4.66%	1.85%		3.20%	1.78%	1.45%		
	(06) NG [/]	(016) Mec[/]	(0K) nc [/]	() () () () () () () () () () () () () (() (00 NG	()]	() () () () () () () () () () () () () ((06) ng [/]	() () () () () () () () () () () () () (() () () () () () () () () () () () () (



For Reference

WITHOUT RS3 Global Static Wear Levelling

<u>WITHOUT</u> Global Static Wear Levelling (<u>WITHOUT</u> TDK SMART SWAP)



Block No; Total [2048] Blocks of 16Gbit 8KB/Page SLC Flash Memory

RESULTS		PASS / FAIL									
	Erased Times	<u>1,000</u>	<u>2,000</u>	<u>3,000</u>	<u>4,000</u>	<u>5,000</u>	<u>6,000</u>	<u>7,000</u>	<u>8,000</u>	<u>9,000</u>	<u>10,000</u>
	Minimum	1	1	1	1	1	1	1	1	1	1
	Maximum	1,000	1,999	2,999	3,999	5,000	5,999	7,000	7,999	9,000	10,500
	%	99.90%	99.90%	99.93%	99.95%	99.98%	99.97%	99.99%	99.98%	99.99%	104.99%
		OK/NG[/]									

会TDK