

## SPECIFICATIONS

A178-01-01F

ITEMS	MODEL		JWT75-522			JWT75-5FF			JWT75-525								
			V1	V2	V3	V1	V2	V3	V1	V2	V3						
1 Nominal Output Voltage		V	+5	+12	-12	+5	+15	-15	+5	+12	-5						
2 Minimum Output Current (*1)		A	0.8	0	0	0.8	0	0	0.8	0	0						
3 Maximum Output Current		A	8.0	4.0	0.5	8.0	3.2	0.5	8.0	4.0	0.5						
4 Maximum Output Power / CH		W	40	48	6.0	40	48	7.5	40	48	2.5						
5 Total Allowable Output Power		W	75			75			75								
6 Efficiency (Typ) (*2)		-	72%														
7 Input Voltage Range (*3)		-	85 - 265VAC (47 - 63Hz) or 120 - 330VDC														
8 Input Current (100/200VAC) (Typ) (*2)		A	1.2 / 0.6														
9 Inrush Current (Typ) (*2,4)		A	14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start														
10 PFHC		-	Designed to meet EN61000-3-2														
11 Power Factor (100/200VAC) (Typ) (*2)		-	0.99 / 0.93														
12 Output Voltage Range		-	5.0 - 5.25	Fixed	Fixed	5.0 - 5.25	Fixed	Fixed	5.0 - 5.25	Fixed	Fixed						
13 Output Voltage Accuracy		-	-	±5%	±5%	-	±5%	±5%	-	±5%	±5%						
14 Maximum Ripple & Noise	0≤Ta≤65°C (*5) -10≤Ta≤0°C	mV	120	150	150	120	150	150	120	150	150						
		mV	160	180	180	160	180	180	160	180	180						
15 Maximum Line Regulation	(*6)	mV	20	48	48	20	60	60	20	48	20						
16 Maximum Load Regulation	(*7)	mV	40	100	150	40	120	150	40	100	100						
17 Temperature Coefficient		-	V1,V2:Less than 0.02% / °C, V3:Less than 0.03% / °C														
18 Over Current Protection	(*8)	A	More than 105%														
19 Over Voltage Protection	(*9)	V	5.7 - 7.0	-	-	5.7 - 7.0	-	-	5.7 - 7.0	-	-						
20 Hold-Up Time (Typ)	(*10)	-	20 ms														
21 Leakage Current	(*11)	-	0.75mA MAX,0.2mA(Typ) at 100VAC / 0.44mA(Typ) at 230VAC														
22 Parallel Operation		-	-														
23 Series Operation		-	-														
24 Operating Temperature	(*12)	-	-10 to +65°C (-10 to +50°C :100%, +65°C :50%)														
25 Operating Humidity		-	30 to 90%RH														
26 Storage Temperature		-	-30 to +85°C														
27 Storage Humidity		-	10 to 95%RH														
28 Cooling		-	Convection Cooling														
29 Withstand Voltage		-	Input - FG:2kVAC(20mA), Input - Output:3kVAC (20mA) Output - FG:500VAC(100mA), for 1min.														
30 Isolation Resistance		-	More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC														
31 Vibration		-	At no operating, 10 - 55Hz (Sweep for 1min) 19.6m/s <sup>2</sup> Constant, X,Y,Z 1h each.														
32 Shock (In package)		-	Less than 196.1m/s <sup>2</sup>														
33 Safety	(*13)	-	Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CSA60950-1, EN60950-1 (Expire date of 60950-1 : 20/12/2020) Designed to meet DENAN														
34 Conducted Emission		-	Designed to meet EN55011 / EN55032-B, FCC-ClassB, VCCI-B.														
35 Radiated Emission		-	Designed to meet EN55011 / EN55032-B, FCC-ClassB, VCCI-B.														
36 Weight (Typ)		-	600g														
37 Size (W x H x D)		mm	42 x 92 x 188 (Refer to Outline Drawing)														

\*Read instruction manual carefully, before using the power supply unit.


=NOTES=

- \*1. For V2, V3 stability, to keep V1 minimum output current.
- \*2. At 100/200VAC, Ta=25°C and maximum output power.
- \*3. For cases where conformance to various safety specs (UL, CSA, EN) are required, input voltage range will be 100 - 240VAC(50/60Hz).
- \*4. No applicable for the inrush current to Noise Filter less than 0.2ms.
- \*5. Measure with JEITA RC-9131 probe, Bandwidth of scope :100MHz.
- \*6. 85 - 265VAC, constant load.
- \*7. Minimum load - Full load, constant input voltage.
- \*8. Constant current limit with automatic recovery.
- \*9. OVP circuit will shut down all outputs, manual reset (Line recycle).
- \*10. At 100/200VAC nominal output voltage and maximum total output power.
- \*11. Measured by the each measuring method of UL, CSA, EN and DENAN (at 60Hz), Ta=25°C.
- \*12. Ratings - Derating at standard mounting.
  - Load (%) is percent of maximum output power or maximum output current, whichever is greater.
  - As for other mountings, refer to derating curve (A178-01-02\_).
- \*13. As for DENAN, designed to meet at 100VAC.

## OUTPUT DERATING

Ta(°C)	LOAD(%)			
	MOUNTING A	MOUNTING B	MOUNTING C	MOUNTING D
-10 ~+35	100	100	100	100
40	100	100	100	83
45	100	100	83	67
50	100	83	67	50
55	83	67	50	
60	67	50		
65	50			

OUTPUT DERATING CURVE

**MOUNTING A****MOUNTING B****MOUNTING C****MOUNTING D****PROHIBIT**

(STANDARD MOUNTING)

