

# **RDEN-048050**

# **SPECIFICATIONS**



A575NAA-RDEN-048050-001 201410


# **RDEN-048050**

Item		Model	RDEN-048050
1	Rated Voltage (DC) *1	V	48 (DC76V max.)
2	Rated Current (DC) *2	A	50
3	Test Voltage (1min DC)	terminals to case	1500 at 20±15°C, 65± 20 %
		between terminals	100 at 20±15°C, 65± 20 %
4	Isolation Resistance (terminals to case, 500V DC, 1 minute after start)	M Ω	500MΩ min. at 20±15°C, 65± 20 %
5	DC Resistance (both lines)	m Ω	3 max.
6	Temperature Rise	°C	40 max.
7	Operating Temperature	°C	-30 ~ +85
8	Operating Humidity	-	30 ~ 95 % RH
9	Storage Temperature	°C	-30 ~ +85
10	Storage Humidity	-	10 ~ 95 % RH
11	Vibration	-	Frequency : 10~55Hz Amplitude : 1.5mm, Sweep for 1 min. Dimension and times : X, Y and Z directions for 2 hours each.
12	Safety Standards	-	UL60950-1, CSA C22.2 No.60950-1, EN60939
13	Weight	g	310

## NOTE

\*1. Use only for a circuit insulated from a primary source with reinforced or double insulation.

\*2. Value for Ta less than 55°C  
For Ta more than 55 °C, derate according to the derating curve shown on the right.



## CAUTION

- Specifications which provide more details for the proper and safe use of the described product are available upon request.
- All specification are subject to change without notice.

A575NAA-RDEN-048050-001 201410