

# FA20X7R2A155KRU06




## Application

Automotive Grade

## Series

FA20



## Dimensions

L 5.5mm Max.  
 W 7mm Max.  
 T 4mm Max.  
 F 5mm +0.8,-0.2mm  
 d 0.5mm +0.1,-0.03mm

## Temperature Characteristic

-55 to 125°C +/-15%

## Rated Voltage

100Vdc

## Capacitance

1.5µF

## Capacitance Tolerance

+/-10%

## Dissipation Factor

3% Max.


## Insulation Resistance

333Mohm Min.


## AEC-Q200

Yes


**|Z| vs. Freq. Characteristic**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristics**



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

December 28, 2015