

# FA14X7S2A224KRU06



## Application

Automotive Grade

## Series

FA14



## Dimensions

L 4.5mm Max.  
 W 5.5mm Max.  
 T 3mm Max.  
 F 2.5mm +0.5,-0.2mm  
 d 0.5mm +0.1,-0.03mm

## Temperature Characteristic

-55 to 125°C +/-22%

## Rated Voltage

100Vdc

## Capacitance

220nF

## Capacitance Tolerance

+/-10%

## Dissipation Factor

5% Max.


## Insulation Resistance

2272Mohm Min.


## AEC-Q200

Yes


**|Z| vs. Freq. Characteristic**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristics**



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

December 28, 2015