

# FA24C0G2W101JNU00



## Application

Automotive Grade

## Series

FA24



## Dimensions

L 4.5mm Max.  
 W 5.5mm Max.  
 T 3mm Max.  
 F 5mm +/-1mm  
 d 0.5mm +0.1,-0.03mm  
 l 7mm +/-2mm

## Temperature Characteristic

-55 to 125°C 0+/-30ppm/°C

## Rated Voltage

450Vdc

## Capacitance

100pF

## Capacitance Tolerance

+/-5%

## Q Factor

1000 Min.


## Insulation Resistance

10000Mohm Min.


## AEC-Q200

Yes


**|Z| vs. Freq. Characteristic**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristics**



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.