

FA26X8R1E225KRU00



Application

Automotive Grade

Series

FA26



Dimensions

- L 5.5mm Max.
- W 6mm Max.
- T 3.5mm Max.
- F 5mm +/-1mm
- d 0.5mm +0.1,-0.03mm
- l 7mm +/-2mm

Temperature Characteristic

-55 to 150°C +/-15%

Rated Voltage

25Vdc

Capacitance

2.2uF

Capacitance Tolerance

+/-10%

Dissipation Factor

3% Max.


Insulation Resistance

227Mohm Min.


AEC-Q200

Yes


|Z| vs. Freq. Characteristic



DC Bias Characteristic



Cap. vs. Freq. Characteristic



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.