

# FG14X5R1H335KRT00



## Application

Commercial Grade

## Series

FG14



## Dimensions

- L 4.5mm Max.
- W 5.5mm Max.
- T 3mm Max.
- F 2.5mm +/-0.8mm
- d 0.5mm +0.1,-0.03mm
- l 7mm +/-2mm

## Temperature Characteristic

-55 to 85°C +/-15%

## Rated Voltage

50Vdc

## Capacitance

3.3uF

## Capacitance Tolerance

+/-10%

## Dissipation Factor

7.5% Max.


## Insulation Resistance

151Mohm Min.


## AEC-Q200

No


**|Z| vs. Freq. Characteristic**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristics**



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

December 28, 2015