

# FA28X7R1H333KNU06



## Application

Automotive Grade

## Series

FA28



## Dimensions

L 4mm Max.  
 W 5.5mm Max.  
 T 2.5mm Max.  
 F 5mm +0.8,-0.2mm  
 d 0.5mm +0.1,-0.03mm

## Temperature Characteristic

-55 to 125°C +/-15%

## Rated Voltage

50Vdc

## Capacitance

33nF

## Capacitance Tolerance

+/-10%

## Dissipation Factor

3% Max.


## Insulation Resistance

10000Mohm Min.


## AEC-Q200

Yes


**|Z| vs. Freq. Characteristic**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristics**



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

December 28, 2015