

# FG14X5R1E156MRT06



## Application

Commercial Grade

## Series

FG14



## Dimensions

L 4.5mm Max.  
 W 5.5mm Max.  
 T 3mm Max.  
 F 2.5mm +0.5,-0.2mm  
 d 0.5mm +0.1,-0.03mm

## Temperature Characteristic

-55 to 85°C +/-15%

## Rated Voltage

25Vdc

## Capacitance

15uF

## Capacitance Tolerance

+/-20%

## Dissipation Factor

10% Max.


## Insulation Resistance

33Mohm Min.


## AEC-Q200

No


**|Z| vs. Freq. Characteristic**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristics**



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

December 28, 2015