

C0603CH1E3R3C030BA

TDK Item Description : C0603CH1E3R3CT****



Application & Main Feature

Commercial Grade (General (Up to 50V))

Series

C0603 [EIA CC0201]



Dimensions

L	0.60mm +/-0.03mm
W	0.30mm +/-0.03mm
T	0.30mm +/-0.03mm
B	0.10mm Min.
G	0.20mm Min.

Temperature Characteristic

CH (-25 to 85 degC 0+/-60ppm/degC)

Rated Voltage

1E (25Vdc)

Capacitance

3.3pF

Capacitance Tolerance

C (+/-0.25pF)

Q Factor

466 Min.


Insulation Resistance

10Gohm Min.


AEC-Q200

Not Applicable


|Z|, ESR vs. Freq. Characteristics



DC Bias Characteristic



Cap. vs. Freq. Characteristic



Temperature Characteristics

