

C0603X6S1A224K030BC

TDK Item Description : C0603X6S1A224KT****



Application & Main Feature

Commercial Grade (General (Up to 50V))

Series

C0603 [EIA CC0201]



Dimensions

L 0.60mm +/-0.05mm
 W 0.30mm +/-0.05mm
 T 0.30mm +/-0.05mm
 B 0.10mm Min.
 G 0.20mm Min.

Temperature Characteristic

X6S (-55 to 105 degC +/-22%)

Rated Voltage

1A (10Vdc)

Capacitance

220nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor

10% Max.


Insulation Resistance

454Mohm Min.


AEC-Q200

Not Applicable


DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



Characterization Sheet (Multilayer Ceramic Chip Capacitors)



All specifications are subject to change without notice.

January 3, 2016