

C2012JB1E155M085AC

TDK Item Description : C2012JB1E155MT****



Application & Main Feature

Commercial Grade (General (Up to 50V))

Series

C2012 [EIA CC0805]

Dimensions

L 2.00mm +/-0.2mm
W 1.25mm +/-0.2mm
T 0.85mm +/-0.15mm
B 0.20mm Min.
G 0.50mm Min.

Temperature Characteristic

JB (-25 to 85 degC +/-10%)

Rated Voltage

1E (25Vdc)

Capacitance

1.5uF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor


5% Max.

Insulation Resistance


66Mohm Min.

AEC-Q200


Not Applicable




DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 3, 2016