

C2012X6S1V335K125AB

TDK Item Description : C2012X6S1V335KT****




Application & Main Feature


Commercial Grade (General (Up to 50V))

Series

C2012 [EIA CC0805]



DC Bias Characteristic



Dimensions

L 2.00mm +/-0.2mm
W 1.25mm +/-0.2mm
T 1.25mm +/-0.2mm
B 0.20mm Min.
G 0.50mm Min.

Temperature Characteristic

X6S (-55 to 105 degC +/-22%)

Rated Voltage

1V (35Vdc)

Capacitance

3.3uF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor

7.5% Max.


Insulation Resistance

151Mohm Min.


AEC-Q200

Not Applicable


|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 3, 2016