

# C2012X7R1V684M125AB

TDK Item Description : C2012X7R1V684MT\*\*\*\*



## Application & Main Feature

Commercial Grade ( General (Up to 50V) )

## Series

C2012 [EIA CC0805]

## Dimensions

L 2.00mm +/-0.2mm  
W 1.25mm +/-0.2mm  
T 1.25mm +/-0.2mm  
B 0.20mm Min.  
G 0.50mm Min.

## Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

## Rated Voltage

1V (35Vdc)

## Capacitance

680nF

## Capacitance Tolerance

M (+/-20%)

## Dissipation Factor


5% Max.

## Insulation Resistance


735Mohm Min.

## AEC-Q200


Not Applicable




## DC Bias Characteristic




## |Z|, ESR vs. Freq. Characteristics




## Temperature Characteristics



## Cap. vs. Freq. Characteristic



## Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 3, 2016