

C2012X7T2W223M125AE

TDK Item Description : C2012X7T2W223MT***S



Application & Main Feature

Commercial Grade (Soft Termination)

Series

C2012 [EIA CC0805]

Dimensions

L	2.00mm +0.45,-0.2mm
W	1.25mm +0.25,-0.2mm
T	1.25mm +0.25,-0.2mm
B	0.20mm Min.
G	0.50mm Min.

Temperature Characteristic

X7T (-55 to 125 degC +22,-33%)

Rated Voltage

2W (450Vdc)

Capacitance

22nF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor


2.5% Max.

Insulation Resistance


10Gohm Min

AEC-Q200


Not Applicable




DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics (Simulation Data)




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

March 16, 2017