

CGA2B3X8R1H682K050BE

TDK Item Description : CGA2B3X8R1H682KT***S




Equivalent C1005X8R1H682K for Automotive

Application & Main Feature


Automotive Grade (Soft Termination)

Series

CGA2(1005) [EIA CC0402]



DC Bias Characteristic



Dimensions

L	1.00mm +0.15,-0.05mm
W	0.50mm +0.1,-0.05mm
T	0.50mm +0.1,-0.05mm
B	0.10mm Min.
G	0.30mm Min.

Temperature Characteristic

X8R (-55 to 150 degC +/-15%)

Rated Voltage

1H (50Vdc)

Capacitance

6.8nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor

3% Max.


Insulation Resistance

10Gohm Min


AEC-Q200

Yes


|Z|, ESR vs. Freq. Characteristics (Simulation Data)




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

March 16, 2017