

CGA3E2X8R1H223M080AE

TDK Item Description : CGA3E2X8R1H223MT***S



Equivalent C1608X8R1H223M for Automotive

Application & Main Feature

Automotive Grade (Soft Termination)

Series

CGA3(1608) [EIA CC0603]

Dimensions

L	1.60mm +0.2,-0.1mm
W	0.80mm +0.15,-0.1mm
T	0.80mm +0.15,-0.1mm
B	0.20mm Min.
G	0.30mm Min.

Temperature Characteristic

X8R (-55 to 150 degC +/-15%)

Rated Voltage

1H (50Vdc)

Capacitance

22nF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor


3% Max.

Insulation Resistance


10Gohm Min

AEC-Q200


Yes




DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics (Simulation Data)




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

March 17, 2017