

CKG45KC0G2J333J290JH

TDK Item Description : CKG45KC0G2J333JT***




Application & Main Feature

Commercial Grade (MEGACAP Type)

Series

CKG45K(4532) [EIA 1812]



Dimensions

L	5.00mm ±0.50mm
W	3.50mm ±0.50mm
T	2.90mm ±0.10mm
E	1.10mm ±0.30mm

Temperature Characteristic

C0G (-55 to 125 degC 0+/-30ppm/degC)

Rated Voltage

2J(630Vdc)

Capacitance

33nF

Capacitance Tolerance

J (±5%)

Q Factor

1000 Min.


Insulation Resistance

10Gohm Min


AEC-Q200

Not Applicable


DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



Characterization Sheet (Multilayer Ceramic Chip Capacitors)



All specifications are subject to change without notice.

May 22, 2019