

## Common mode filters

## Automobile Ultra-high-speed differential signal line

## KCZ-DH series



AEC-Q200

## KCZ1210DH type



## FEATURES

- Multilayer common mode filter for ultra-high speed differential signal lines that supports 125°C.
- Guide electric property resin absorbs external stress, and mechanical stress, resistance force to thermal shock is improved.
- Since the cutoff frequency of the differential mode supports up to 6.0 GHz, it is ideal for high-speed differential transmission lines such as USB3.0.
- Differential mode cutoff frequency is 100Ω typ.
- Operating temperature range: -55 to +125°C

## APPLICATION

- Differential transmission interfaces such as cameras, displays, infotainment, etc. (LVDS, GVI, USB3.0 etc.)

## PART NUMBER CONSTRUCTION

KCZ	1210	DH	500	HR	T	D25
Series name	LxWxT dimensions 1.25x1.0x0.5 mm	Product internal code	Impedance (Ω) at 100MHz	Category	Packaging style	Internal code

## CHARACTERISTICS SPECIFICATION TABLE


Common mode impedance [100MHz]		DC resistance [1 line]	Rated current	Rated voltage	Insulation resistance	Part No.
(Ω)	Tolerance	(Ω)max.	(mA)max.	(V)max.	(MΩ)min.	
12	±5Ω	1.5	100	5	10	<a href="#">KCZ1210DH120HRTD25</a>
45	±25%	2.5	100	5	10	<a href="#">KCZ1210DH500HRTD25</a>

\* Impedance (Ω) at 100MHz in PART NUMBER CONSTRUCTION is a reference value.

## Measurement equipment


Measurement item	Product No.	Manufacturer
Common mode impedance	4991A+16192A	Keysight Technologies
DC resistance	Type-755611	Yokogawa
Insulation resistance	4339B	Keysight Technologies

\* Equivalent measurement equipment may be used.



# KCZ1210DH type

## ■ IMPEDANCE VS. FREQUENCY CHARACTERISTICS




Measurement equipment

Product No.	Manufacturer
4991A+16192A	Keysight Technologies

\* Equivalent measurement equipment may be used.


# KCZ1210DH type

## SHAPE & DIMENSIONS




Dimensions in mm

## RECOMMENDED LAND PATTERN




Dimensions in mm

## CIRCUIT DIAGRAM




• No polarity

## RECOMMENDED REFLOW PROFILE




## PACKAGING STYLE

### REEL DIMENSIONS




Dimensions in mm

### TAPE DIMENSIONS



Dimensions in mm

Type	A	B	K
KCZ1210DH	1.17±0.03	1.40±0.03	0.63±0.03



Dimensions in mm

### PACKAGE QUANTITY

Package quantity	4,000 pcs/reel
------------------	----------------

### TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range	Storage temperature range*	Individual weight
-55 to +125 °C	-55 to +125 °C	3.0 mg

\* The storage temperature range is for after the assembly.

# REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

## SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

### REMINDERS

- The storage period is within 6 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less).  
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- Before soldering, be sure to preheat components.  
The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
- Soldering corrections after mounting should be within the range of the conditions determined in the specifications.  
If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
- Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- Carefully lay out the coil for the circuit board design of the non-magnetic shield type.  
A malfunction may occur due to magnetic interference.
- Use a wrist band to discharge static electricity in your body through the grounding wire.
- Do not expose the products to magnets or magnetic fields.
- Do not use for a purpose outside of the contents regulated in the delivery specifications.
- The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.  
The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.  
If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.