

# CKG57KX7R2E474M335JH

TDK item description : CKG57KX7R2E474MT\*\*\*




## Application & Main Feature

Commercial grade (MEGACAP)

## Series

CKG57K(5750) [EIA 2220]



## Dimensions

L 6.00±0.50 mm  
W 5.00±0.50 mm  
T 3.35±0.15 mm  
E 1.60±0.30 mm

## Temperature Characteristic

X7R (-55 to +125 degC, ±15%)

## Rated Voltage

2E (250Vdc)

## Capacitance

470nF

## Capacitance Tolerance

M (±20%)

## DF

3 % max.


## Insulation Resistance

1063 Mohm min.


## AEC-Q200

Not Applicable


## DC Bias Characteristic




## |Z|, ESR vs. Freq. Characteristics




## Temperature Characteristics



## Cap. vs. Freq. Characteristic



## Ripple Temperature Rise Characteristics



Characterization Sheet ( Multilayer Ceramic Chip Capacitors )



All specifications are subject to change without notice.

April 7, 2022