

CKG57NC0G2E304J500JH

TDK Item Description : CKG57NC0G2E304JT***




Application & Main Feature

Commercial Grade (MEGACAP Type)

Series

CKG57N(5750) [EIA 2220]



Dimensions

L	6.00mm ±0.50mm
W	5.00mm ±0.50mm
T	5.00mm ±0.50mm
E	1.60mm ±0.30mm

Temperature Characteristic

C0G (-55 to 125 degC 0+/-30ppm/degC)

Rated Voltage

2E(250Vdc)

Capacitance

300nF

Capacitance Tolerance

J (±5%)

Q Factor

1000 Min.


Insulation Resistance

1.666Gohm Min


AEC-Q200

Not Applicable


DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics



Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics

