

# CNA6P1X7R1E226M250AE

TDK item description : CNA6P1X7R1E226MT\*\*\*A




## Application & Main Feature

Automotive grade (Soft termination (Low resistance))

## Series

CNA6(3225) [EIA 1210]



## Dimensions

L 3.20±0.30 mm  
 W 2.50±0.30 mm  
 T 2.50±0.30 mm  
 B 0.50 mm min.  
 G ---

## Temperature Characteristic

X7R (-55 to +125 degC, ±15%)

## Rated Voltage

1E (25Vdc)

## Capacitance

22µF

## Capacitance Tolerance

M (±20%)

## DF






5 % max.

## Insulation Resistance

22 Mohm min.

## AEC-Q200

Yes



Characterization Sheet ( Multilayer Ceramic Chip Capacitors )



All specifications are subject to change without notice.

February 16, 2022