

File E62388  
Project 07SC02610

July 11, 2007

REPORT

On

COMPONENT - ELECTROMAGNETIC INTERFERENCE FILTERS

TDK Corp. Inductive Devices Div.  
YURI-GUN, Japan

Copyright © 2007 Underwriters Laboratories Inc.

Underwriters Laboratories Inc. authorizes the above-named company to reproduce this Report provided it is reproduced in its entirety.

Underwriters Laboratories Inc. authorizes the above-named company to reproduce that portion of this Report consisting of this Cover Page through Page 3.

## DESCRIPTION

## PRODUCT COVERED:

USR Component - Electromagnetic Interference Appliance Filters,

**Models** RSEN-2003, RSEN-2006, RSEN-2010, RSEN-2016, RSEN-2020, RSEN-2030, RSEN-2040, RSEN-2050 **and** RSEN-2060.

**Models** RSEN-2003L, RSEN-2006L, RSEN-2010L, RSEN-2016L, RSEN-2020L, RSEN-2030L, RSEN-2040L, RSEN-2050L **and** RSEN-2060L.

**Models** RSAN-2003, RSAN-2006, RSAN-2010, RSAN-2016, RSAN-2020, RSAN-2030, \*RSAN-2040, RSAN-2050 **and** RSAN-2060.

**Models** RSAN-2003L, RSAN-2006L, RSAN-2010L, RSAN-2016L, RSAN-2020L, RSAN-2030L, RSAN-2040L, RSAN-2050L **and** RSAN-2060L.

**Models** RSEN-2003D, RSEN-2006D, RSEN-2010D, RSEN-2016D, RSEN-2020D **and** RSEN-2030D.

**Models** RSEN-2003LD, RSEN-2006LD, RSEN-2010LD, RSEN-2016LD, RSEN-2020LD **and** RSEN-2030LD.

**Models** RSAN-2003D, RSAN-2006D, RSAN-2010D, RSAN-2016D, RSAN-2020D **and** RSAN-2030D.

**Models** RSAN-2003LD, RSAN-2006LD, RSAN-2010LD, RSAN-2016LD, RSAN-2020LD **and** RSAN-2030LD.

\*

## ELECTRICAL RATINGS:

Catalog. No.	Volts (V ac)	Current (A)	Frequency. (Hz)	Phase	Maximum Ambient (°C)
RSEN-2003 RSEN-2003L RSEN-2003D RSEN-2003LD	250	3	50/60	1	55
RSEN-2006 RSEN-2006L RSEN-2006D RSEN-2006LD	250	6	50/60	1	55
RSEN-2010 RSEN-2010L RSEN-2010D RSEN-2010LD	250	10	50/60	1	55
RSEN-2016 RSEN-2016L RSEN-2016D RSEN-2016LD	250	16	50/60	1	55
RSEN-2020 RSEN-2020L RSEN-2020D RSEN-2020LD	250	20	50/60	1	55
RSEN-2030 RSEN-2030L RSEN-2030D RSEN-2030LD	250	30	50/60	1	55
RSEN-2040 RSEN-2040L	250	40	50/60	1	55
RSEN-2050 RSEN-2050L	250	50	50/60	1	55
RSEN-2060 RSEN-2060L	250	60	50/60	1	55

## ELECTRICAL RATINGS (CONT.):

Catalog. No.	Volts (V ac)	Current (A)	Frequency. (Hz)	Phase	Maximum Ambient (°C)
RSAN-2003 RSAN-2003L <b>RSAN-2003D</b> <b>RSAN-2003LD</b>	250	3	50/60	1	55
RSAN-2006 RSAN-2006L <b>RSAN-2006D</b> <b>RSAN-2006LD</b>	250	6	50/60	1	55
RSAN-2010 RSAN-2010L <b>RSAN-2010D</b> <b>RSAN-2010LD</b>	250	10	50/60	1	55
RSAN-2016 RSAN-2016L <b>RSAN-2016D</b> <b>RSAN-2016LD</b>	250	16	50/60	1	55
RSAN-2020 RSAN-2020L <b>RSAN-2020D</b> <b>RSAN-2020LD</b>	250	20	50/60	1	55
RSAN-2030 RSAN-2030L <b>RSAN-2030D</b> <b>RSAN-2030LD</b>	250	30	50/60	1	55
RSAN-2040 RSAN-2040L	250	40	50/60	1	55
RSAN-2050 RSAN-2050L	250	50	50/60	1	55
RSAN-2060 RSAN-2060L	250	60	50/60	1	55

\*

## NOMENCLATURE:

Example: RSEN-2003LD

RSEN	-	2	003	L	D
I		II	III	IV	V

I - &lt;Model Name&gt;

RSEN  
RSAN

II - &lt;Rated Voltage&gt;

2: 250 V

III - &lt;Rated Current&gt;

003: 3 A  
006: 6 A  
010: 10 A  
016: 16 A  
020: 20 A  
030: 30 A  
040: 40 A  
050: 50 A  
060: 60 A

IV - &lt;Filter Construction&gt;

None: with Y capacitors  
L: without Y capacitors

V - &lt;Filter Chassis&gt;

None: Standard type  
D: Din rail type

## TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

For use only in complete equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc. The following are among the features which should be judged during the investigation of the equipment in which this filter is used:

Models have been judged on the basis of the spacing requirements in the Standard for Electromagnetic Interference Filters (UL 1283 Fifth Edition) which would cover the component itself if submitted for unrestricted Listing.

USR - Indicates investigation to the Standard for Electromagnetic Interference Filters, UL 1283, Fifth Edition, latest revision dated July 31, 2007.

## Conditions of Acceptability -

1. Leakage current shall be measured in the end-product to determine compliance with the applicable end-product requirements.
2. The end product shall not rely on the filter for grounding.
3. The filter shall be provided with an overall enclosure suitable for the applicable end-product requirements.
4. The electrical ratings specified shall not be exceeded.
5. These filters are not intended for use in radio, television, video, telephone, or telephone power supply type appliances.
6. The terminals have not been evaluated as field wiring terminals and shall be used for factory wiring only.
7. Suitability of mounting is to be determined in the end use product.
8. Suitability of grounding is to be determined in the end use product.
9. Polymeric covers have not been evaluated for mechanical strength of insulation.
10. **Abnormal Operating Test (Limited Short Circuit) at alternate current has been conducted as follows, tested using a 60 A fuse of type RK1:**

Model	Test current [A]
RSEN-2060	5000