

ENEC LICENSE

License No. ENEC-01674-A1
Page 1/2
Date of Issue 2020-07-06

License Holder TDK Corporation
Electronic Components Business Company
Magnetics Business Group
1-11 Kabayachi, Kisakata-Machi
Nikaho-Shi, 018-0146 Akita-Ken Japan

Production site Guangxi Real Faith Pingzhou Electronics Co Ltd
No. 81 Yong An Road Longxu Town
Longxu District
Wuzhou, 543100 Guangxi China

Certification Mark See Annex 1

Certified Product EMI FILTER

Model RSEV-2006, RSEV-2006L, RSEV-2010, RSEV-2010L,
RSEV-2016, RSEV-2016L, RSEV-2020, RSEV-2020L,
RSEV-2030, RSEV-2030L

Trademark ***TDK-Lambda***

Rated Voltage / Frequency 250V, , 50/60 Hz

Rated Current / Power 6A~30A See Test Report for details.

Insulation Class -

Degree of protection (IP) -

Tested acc. to EN 60939-3:2015

Test Report No. E62388-D1-ENEC-Original issued on 2020-07-01

Additional The report was revised to include administrative modifications.
This certificate replaces earlier issued ENEC-01674-M1 to
change the name of factory.

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Annex 1 to License No.

ENEC-01674-A1

Annex of the form of the Mark



* Identification number of the Certification Body

Size of the mark:

The size of the mark may be reduced on the condition that it remains legible and that the ratio $b/a=1,7$ is kept

Certification Body

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

