



Ref. Certif. No.

**SE-51065A5/M2**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product	Filter unit for radio interference suppression
Name and address of the applicant	TDK Corporation Electronic Components Business Company, Magnetics Business Group, 1-11, Kabayachi, Kisakata-Machi, Nikaho-shi, Akita-ken 018-0146, JAPAN
Name and address of the manufacturer	Same as applicant
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	Guangxi Wuzhou City Pingzhou Electronics Co., Ltd., No. 81, Yong An Road, Longxu Town, Longxu District, Wuzhou City, Guangxi Province, 543100, CHINA
Ratings and principal characteristics	3x6, 10, 16, 20, 30, 40, 50, 60, 80, 100, 150, 200, 250, 300A.250VAC or 500VAC. 50°C. 25/100/21 or 25/085/21. See page 2-3
Trademark (if any)	TDK-Lambda
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	RTEN-50**(D), RTAN-50**(D), RTCN-50**, RTEN-2***, RTHN-2***
Additional information (if necessary may also be reported on page 2)	Replaces CB certificate SE-51065A5/M1 dated 1 July 2013 due to added types RTEN-50** <u>D</u> , RTAN-50** <u>D</u> . See page 2-3
A sample of the product was tested and found to be in conformity with	IEC 60939-1:2010 IEC 60939-2:2005
As shown in the Test Report Ref. No. which forms part of this Certificate	1720154STO-001, -002 + 1816009STO-001

This CB Test Certificate is issued by the National Certification Body

**Intertek Semko AB**  
Box 1103  
SE-164 22 Kista, Sweden  
Int +46 8 750 00 00

Date: 30 October 2018



Signature:

Paul Klemets

## Additional information (if necessary)

RTEN-5006(D)	3x6A	3x4.5mH		
RTEN-5010(D)	3x10A	3x2.1mH		
RTEN-5016(D)	3x16A	3x0.79mH		
RTEN-5020(D)	3x20A	3x1.6mH		
RTEN-5030(D)	3x30A	3x0.61mH		
RTEN-5040	3x40A	3x0.91mH		
RTEN-5050	3x50A	3x0.51mH		
RTEN-5060	3x60A	3x0.36mH		
RTAN-5006(D)	3x6A	3x2.9mH		
RTAN-5010(D)	3x10A	3x1.3mH		
RTAN-5016(D)	3x16A	3x0.51mH		
RTAN-5020(D)	3x20A	3x1.0mH		
RTAN-5030(D)	3x30A	3x0.39mH		
RTAN-5040	3x40A	3x0.59mH		
RTAN-5050	3x50A	3x0.33mH		
RTAN-5060	3x60A	3x0.23mH		
RTCN-5006	3x6A	3x4.5mH		
RTCN-5010	3x10A	3x2.1mH		
RTCN-5016	3x16A	3x0.79mH		
RTCN-5020	3x20A	3x1.6mH		
RTCN-5030	3x30A	3x0.61mH		
RTCN-5040	3x40A	3x0.91mH		
RTCN-5050	3x50A	3x0.51mH		
RTCN-5060	3x60A	3x0.36mH		
RTEN-2006	3 x 6A	3 x 4.5mH	6 x 1uF	6 x 1Mohm
RTEN-2010	3 x 10A	3 x 2.1mH	6 x 1uF	6 x 1Mohm
RTEN-2016	3 x 16A	3 x 0.79mH	6 x 1uF	6 x 1Mohm
RTEN-2020	3 x 20A	3 x 1.6mH	6 x 1.5uF	6 x 1Mohm
RTEN-2030	3 x 30A	3 x 0.61mH	6 x 1.5uF	6 x 1Mohm
RTEN-2040	3 x 40A	3 x 0.91mH	6 x 3.3uF	6 x 0.47Mohm
RTEN-2050	3 x 50A	3 x 0.51mH	6 x 3.3uF	6 x 0.47Mohm
RTEN-2060	3 x 60A	3 x 0.36mH	6 x 3.3uF	6 x 0.47Mohm
RTEN-2080	3 x 80A	3 x 0.64mH	6 x 4.7uF	6 x 0.47Mohm
RTEN-2100	3 x 100A	3 x 0.64mH	6 x 4.7uF	6 x 0.47Mohm
RTEN-2150	3 x 150A	3 x 0.67mH	6 x 4.7uF	6 x 0.47Mohm
RTEN-2200	3 x 200A	3 x 0.42mH	6 x 4.7uF	6 x 0.47Mohm
RTEN-2250	3 x 250A	3 x 0.24mH	6 x 4.7uF	6 x 0.47Mohm
RTEN-2300	3 x 300A	3 x 0.11mH	6 x 4.7uF	6 x 0.47Mohm

Date: 30 October 2018

Signature: 

RTHN-2006	3 x 6A	6 x 4.5mH
RTHN-2010	3 x 10A	6 x 2.1mH
RTHN-2016	3 x 16A	6 x 0.79mH
RTHN-2020	3 x 20A	6 x 1.6mH
RTHN-2030	3 x 30A	6 x 0.61mH
RTHN-2040	3 x 40A	6 x 0.91mH
RTHN-2050	3 x 50A	6 x 0.51mH
RTHN-2060	3 x 60A	6 x 0.36mH
RTHN-2080	3 x 80A	6 x 0.64mH
RTHN-2100	3 x 100A	6 x 0.64mH
RTHN-2150	3 x 150A	6 x 0.67mH
RTHN-2200	3 x 200A	6 x 0.42mH
RTHN-2250	3 x 250A	6 x 0.24mH
RTHN-2300	3 x 300A	6 x 0.11mH

RTEN-50\*\*D: DIN rail attachment assembled

RTAN-50\*\*D: DIN rail attachment assembled

Date: 30 October 2018

Signature: 