

RSEG & RSAG SERIES


SPECIFICATIONS

Items	Model		RSEG-20R5, RSAG-20R5	RSEG-2001, RSAG-2001	RSEG-2002, RSAG-2002	RSEG-2003, RSAG-2003	RSEG-2004, RSAG-2004	RSEG-2006, RSAG-2006
	1	Rated Voltage (AC, DC)	V	250				
2	Rated Current (AC, DC) *1	A	0.5	1	2	3	4	6
3	Test Voltage (terminals to base plate, 1min AC)	V	1500 at 20±15°C, 65± 20 %					
4	Isolation Resistance (terminals to base plate, 500V DC)	M Ω	100 min. at 20±15°C, 65± 20 %					
5	Leakage Current	250V, 60Hz	0.75 max.					
6	DC Resistance (both lines)	m Ω	400	350	310	150	130	100
7	Temperature Rise	°C	30 max.					
8	Operating Temperature	°C	-25 ~ +85					
9	Operating Humidity	-	15 ~ 85 % RH					
10	Storage Temperature	°C	-25 ~ +85					
11	Storage Humidity	-	5 ~ 85 % RH					
12	Vibration	-	Frequency : 10~55Hz Amplitude : 1.5mm, Sweep for 1 min. Dimension and times : X, Y and Z directions for 2 hours each.					
13	Safety Standards *2	-	Compliant with EN60939 (SEMKO), UL1283 and CSA C22.2 No.8					
14	Weight	g	14	14	14	14	≒25	≒25

NOTE

*1 Value for Ta less than 55 °C (include 55 °C)
 For Ta more than 55 °C (not include 55 °C)
 According to the derating curve shown on the right.

*2 Before approval



CAUTION

- Specifications which provide more details for the proper and safe use of the described product are available upon request.
- All specification are subject to change without notice.