


CFast™

CAE3B



GENERAL INFORMATION

TYPE	CFast™
INTERFACE	Serial ATA Revision 2.6
DATA TRANSFER MODE	SATA 1.5Gbps, 3.0Gbps
CONNECTOR	CFast™ Type I
OUTLINE DIMENSIONS	36.4 x 42.8 x 3.6 mm
SERIES	CAE3B
CONTROLLER TYPE	 TDK GBDriver RS3
FLASH TYPE	SLC
DENSITY RANGE	512 MB - 8 GB
DATA RETENTION	10 years @ life begin-10% 1 year @ life end
ENDURANCE ENTERPRISE WL	512 MB ~ 8 GB: 50,000 P/E Cycles *Flash Block Level

TEMPERATURE

OPERATING TEMPERATURE	Commercial: 0°C to +70°C Industrial: -40°C to +85°C
STORAGE TEMPERATURE	Commercial: -25°C to +85°C Industrial: -40°C to +85°C

PERFORMANCE

Read (max.)	105 MByte/sec
Write (max.)	60 MByte/sec

ROBUSTNESS

MTBF	≥ 2,000,000 hours
SHOCK	1500G, 0.5ms
VIBRATION	20G, 10-2000Hz
HUMIDITY	0 to 90 % RH (No condensation)

ELECTRICAL DATA

VOLTAGE	3.3 V ± 5 %
POWER CONSUMPTION	<ul style="list-style-type: none"> - Single mode Read Write: 125mA max. - 2ch mode Read Write: 215mA max. - 4ch mode Read Write: 365mA max. - Slumber: less than 50mA

FEATURE LIST

FEATURES & TOOLS	<ul style="list-style-type: none"> - In-House Designed Controller (HW/FW) <ul style="list-style-type: none"> - Power Fail Data Safety - Global static wear leveling <ul style="list-style-type: none"> - SMART - NCQ, TRIM - AES 128bit encryption
PART NUMBER	CAE3BxxxxTxxxB00EAA0