


Half Slim

SHT2A



GENERAL INFORMATION

TYPE	Half Slim			
INTERFACE	Serial ATA Revision 3.2			
DATA TRANSFER MODE	SATA 1.5Gbps, 3.0Gbps, 6.0Gbps			
CONNECTOR	15 + 7 pin Serial ATA			
OUTLINE DIMENSIONS	54 x 39 mm			
SERIES	SHT2A			
CONTROLLER TYPE	TDK GBDriver GS2			
FLASH TYPE	3D - SLC mode		3D - TLC mode	
	3D - Gen3	3D - Gen4	3D - Gen3	3D - Gen4
DENSITY RANGE	8 GB - 256GB	32 GB - 512 GB	25 GB - 800 GB	100 GB - 1600 GB
DATA RETENTION	10 years @ life begin 1 year @ life end			
ENDURANCE	30,000 P/E Cycles		3,000 P/E Cycles	
ENTERPRISE WL	*Flash Block Level		*Flash Block Level	

TEMPERATURE

OPERATING TEMPERATURE	Commercial: 0°C to +70°C Industrial: -40°C to +85°C
STORAGE TEMPERATURE	Commercial: -25°C to +85°C Industrial: -40°C to +85°C

PERFORMANCE

Read (max.)	345 MByte/sec
Write (max.)	295 MByte/sec

ROBUSTNESS

MTBF	≥ 2,000,000 hours
SHOCK	1500G,0.5ms
VIBRATION	20G,10-2000Hz
HUMIDITY	0 to 90 % RH (No condensation)

ELECTRICAL DATA

VOLTAGE	5 V ± 10 %
POWER CONSUMPTION (*RT)	- Read: 1000 mW max. - Write: 1150 mW max. - Slumber: less than 60mA

FEATURE LIST

FEATURES & TOOLS	<ul style="list-style-type: none"> - In-House Designed Controller (HW/FW) <ul style="list-style-type: none"> - SLC Cache, LDPC-ECC, RAID - Temperature monitoring function - Write-protected area setting tool (on request) <ul style="list-style-type: none"> - DRAM-less Design - Power Fail Data Safety - Power Back-up Circuit - Global static wear leveling <ul style="list-style-type: none"> - SMART (life monitor) - NCQ, TRIM - AES 256 bit encryption (on request)
PART NUMBER	SHT2AxxxxKxxxA00ESA0 SHT2AxxxxKxxxA00ESA0 SHT2AxxxxKxxxA00ESA0 SHT2AxxxxKJxxA00ESA0