


FB Series

Wet molding process / Higher power La-Co type FB12B

Demagnetization curve



Magnetic characteristics

Material	FB12B		
Residual magnetic flux density B_r	(mT)	470 ± 10	$(4.7 \pm 0.1 \text{ kG})$
Coercive force H_{cB}	(kA/m)	340 ± 12	$(4.3 \pm 0.15 \text{ kOe})$
Intrinsic coercive force H_{cJ}	(kA/m)	380 ± 12	$(4.8 \pm 0.15 \text{ kOe})$
Maximum energy product $(BH)_{\text{max}}$	(kJ/m ³)	43.1 ± 1.6	$(5.4 \pm 0.2 \text{ MGOe})$

△ The details can be found by referring to the appended individual delivery specifications.
All specifications are subject to change without notice.