


FB Series

Wet molding process / La-Co free type

FB6H

NRND

Demagnetization curve



Magnetic characteristics

Material	FB6H		
Residual magnetic flux density B_r	(mT)	400 ± 10	$(4.0 \pm 0.1 \text{ kG})$
Coercive force H_{cB}	(kA/m)	302.4 ± 12	$(3.8 \pm 0.15 \text{ kOe})$
Intrinsic coercive force H_{cJ}	(kA/m)	358.1 ± 12	$(4.5 \pm 0.15 \text{ kOe})$
Maximum energy product $(BH)_{max}$	(kJ/m³)	30.3 ± 1.6	$(3.8 \pm 0.2 \text{ MGOe})$

△ The details can be found by referring to the appended individual delivery specifications.
All specifications are subject to change without notice.