


FB Series

Wet molding process / La-Co free type

FB6N

NRND

Demagnetization curve



Magnetic characteristics

Material	FB6N		
Residual magnetic flux density B_r	(mT)	440 ± 10	$(4.4 \pm 0.1 \text{ kG})$
Coercive force H_{cB}	(kA/m)	258.6 ± 12	$(3.25 \pm 0.15 \text{ kOe})$
Intrinsic coercive force H_{cJ}	(kA/m)	262.6 ± 12	$(3.3 \pm 0.15 \text{ kOe})$
Maximum energy product $(BH)_{max}$	(kJ/m³)	36.7 ± 1.6	$(4.6 \pm 0.2 \text{ MGOe})$

△ The details can be found by referring to the appended individual delivery specifications.
All specifications are subject to change without notice.