



Unless otherwise specified dimensional tolerance as follows:	
DIMENSION (mm)	TOLERANCE ± mm
L ≤ 16	0.2
16 < L ≤ 63	0.2
63 < L ≤ 250	0.3
250 < L	0.5



NOTE:

- A : Ø3.5 HOLES FOR CUSTOMER CHASSIS MOUNTING.
- B : M3 TAPPED & EMBOSSED HOLES FOR CUSTOMER CHASSIS MOUNTING.
- C : Ø3.5 HOLES FOR CUSTOMER CHASSIS MOUNTING.
- D : M3 TAPPED & STANDOFF HOLES FOR FG CONNECTION.
- E : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, SAFETY MARKING(FOR ONLY APPROVED PRODUCTS) AND COUNTRY OF MANUFACTURE ARE SHOWN HERE IN ACCORDANEC WITH THE SPECIFICATIONS.

CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	B2P3-VH(LF)(SN)	J.S.T	1
PIN HEADER (OUTPUT SIDE CN51)	B4P-VH(LF)(SN)	J.S.T	1

MATCHING HOUSINGS, PINS & TOOL (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
SOCKET HOUSING(CN1)	VAR-2/VHR-3N	J.S.T	1
SOCKET HOUSING(CN51)	VHR-4N	J.S.T	1
TERMINAL PINS	SVH-41T-P1.1 BVH-41T-P1.1	J.S.T	6
HAND CRIMPING TOOL	YC-930R	J.S.T	-
	YC-931R		

(unit : mm)

MODEL NAME	CUS100MB/A
<b>TDK-Lambda</b>	
CA833-02-01/A-D	