



**CONNECTORS USED:**

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	B3P5-VH	JST	1
PIN HEADER(OUTPUT SIDE CN51)	B8P-VH	JST	1

\*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

**MATCHING HOUSINGS AND PINS(NOT INCLUDED WITH THE PRODUCT):**

SOCKET HOUSING (CN1)	VHR-5N	JST	1
SOCKET HOUSING (CN51)	VHR-8N	JST	1
TERMINAL PINS	SVH-21T-P1.1	JST	11

HAND CRIMPING TOOL : YC-160R CN1,CN51 MANUFACTURER : JST

**NOTES**

- A: THE 2-M3 TAPPED & STANDOFF FOR CUSTOMER CHASSIS MOUNTING.SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 5mm.
- B: THE 2-M4 EMBOSSED TAPPED & COUNTER-SUNK HOLES FOR CUSTOMER CHASSIS MOUNTING DEDICATED TO OPTION MODEL /A AND CAN NOT BE USED AT THIS MODEL. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 8mm.
- C: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, NOMINAL OUTPUT CURRENT, PEAK OUTPUT CURRENT AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS)ARE SHOWN ON THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS. COUNTRY OF MANUFACTURE WILL BE SHOWN ON THE NAME PLATE.
- D:  $\perp$  IS FOR SAFETY GROUND CONNECTION.

(unit : mm)

MODEL NAME	CUT75/L
<b>TDK-Lambda</b>	

CA809-02-01/L-C