


**CONNECTORS USED:**

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
CN1	HOUSING	350766-1	TE Connectivity 1
	TERMINAL PINS	350218-1	TE Connectivity 3
CN51A/CN51B	M4 TERMINAL		2
CN61	B8B-PHDSS(LF)(SN)	J.S.T	1

**RECOMMENDED MATCHING HOUSINGS, PINS & TOOL  
(NOT INCLUDED WITH THE PRODUCT):**

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
CN1	SOCKET HOUSING	350766-1	1
	TERMINAL PINS	350536-1	TE Connectivity 3
	HAND CRIMPING TOOL	91500-1	-
CN61	SOCKET HOUSING	PHDR-08VS	J.S.T 1
	TERMINAL PINS	SPHD-001T-P0.5	J.S.T 8
	HAND CRIMPING TOOL	YC-610R, YC-611R	-

**PIN CONFIGURATION AND FUNCTIONS OF CN61**



PIN No.	FUNCTION
1	STBY+: STANDBY SUPPLY + (5V+)
2	STBY-: STANDBY SUPPLY - (5V-)
3	S+: REMOTE SENSE+
4	S-: REMOTE SENSE-
5	NO CONNECTION
6	PG: POWER GOOD SIGNAL
7	R+: REMOTE ON/OFF TERMINAL +
8	R-: REMOTE ON/OFF TERMINAL -

- NOTE:**
- A: 12-M3 TAPPED & STANDOFF HOLES FOR CUSTOMER'S CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION AND EMI SPEC. RECOMMENDED TORQUE : 0.49N·m(5kgf·cm).
  - B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, AND MAXIMUM OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
  - C: COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
  - D: M4 SCREWS(2) FOR O/P TB, RECOMMENDED TORQUE: 1.18N·m(12kgf·cm) MAX

(unit : mm)

MODEL NAME	CUS600M/EF
<b>TDK-Lambda</b>	
CA878-02-01/EF-C	