

CONNECTORS USED :

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (INPUT SIDE CN1)	1-1123724-3	TE	1
PIN HEADER (OUTPUT CN51)	1-1123723-6	TE	1

*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 7.5A.

MATCHING HOUSINGS AND PINS(INCLUDED WITH THE PRODUCT):

SOCKET HOUSING (CN1)	1-1123722-5	TE	1
SOCKET HOUSING (CN51)	1-1123722-6	TE	1
TERMINAL PINS	1123721-1	TE	9


HAND CRIMPING TOOL : 91579-1, MANUFACTURER : TE

NOTES :

- A : THE 5XØ3.5 HOLES ARE CUSTOMER CHASSIS MOUNTING HOLES AND INSERT SPACER (MAX Ø6.2) OF HEIGHT OVER 8mm TO LIFT THE UNIT.ALL MUST BE SCREWED AND GROUNDED.
- B : MODEL NAME, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C : COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
- D : TO KEEP THE DISTANCE MORE THAN 4mm BETWEEN PC-BOARD EDGE AND CUSTOMER CHASSIS.

NAME PLATE

SEE NOTE B



SEE NOTE C

(unit : mm)

MODEL NAME	CUS90E/C02
TDK-Lambda	

CA824-02-01/C02