



== NOTES ==

A: 4- $\phi$ 3.5 HOLES ARE FOR CUSTOMER'S CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.

B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

C:  $\perp$  IS FOR SAFETY GROUND CONNECTION.

D: TO KEEP THE DISTANCE MORE THAN 4mm BETWEEN PCB EDGE AND CUSTOMER'S CHASSIS.

E: OPTION MODEL (OPTION CODE : /R)  
 REMOTE ON/OFF CONTROL CONNECTOR (CN52) : B2B-XH-AM (JST)  
 MATCHING HOUSING : XHP-2 (JST)  
 MATCHING TERMINAL : BXH-001T-P0.6 (JST) OR SXH-001T-P0.6 (JST)  
 HAND CRIMPING TOOL : YC-110R (JST) OR YRS-110 (JST)  
 MATCHING HOUSING AND TERMINAL --- NOT INCLUDED WITH THE PRODUCT

F: VR1 SHOULD NOT BE TOUCHED BECAUSE VR1 IS COATED A FIXING MATERIAL.

== ACCESSORIES ==

\* TERMINAL COVER FOR BARRIER TERMINAL STRIP ---1 (ATTACHED ON OUTPUT TERMINAL TB51 AT SHIPMENT)

(unit : mm)

MODEL NAME	EVS300W
<b>TDK-Lambda</b>	
A269-02-01A	