



Unless otherwise specified dimensional tolerance as follows:

DIMENSION (mm)	TOLERANCE ± mm
$L \leq 16$	0.2
$16 < L \leq 63$	0.2
$63 < L \leq 250$	0.3
$250 < L$	0.5



CUSTOMER MOUNTING HOLE INDICATION(TOP SIDE VIEW)



NOTE:

- A : $\phi 3.5$ HOLES FOR CUSTOMER CHASSIS MOUNTING.
- B : M3 TAPPED & EMBOSSED HOLES FOR CUSTOMER CHASSIS MOUNTING.
- C : M3 TAPPED & STANDOFF HOLES FOR FG CONNECTION.
- D : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, NOMINAL OUTPUT CURRENT, PEAK OUTPUT CURRENT AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS)ARE SHOWN ON THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS. COUNTRY OF MANUFACTURE WILL BE SHOWN ON THE NAME PLATE.

CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	B3P5-VH(LF)(SN)	J.S.T	1
PIN HEADER (OUTPUT SIDE CN51)	B5P-VH(LF)(SN)	J.S.T	1

MATCHING HOUSINGS, PINS & TOOL (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
SOCKET HOUSING(CN1)	VHR-5N	J.S.T	1
SOCKET HOUSING(CN51)	VHR-5N	J.S.T	1
TERMINAL PINS	SVH-21T-P1.1	J.S.T	8
	BVH-41T-P1.1		
HAND CRIMPING TOOL	YC-930R	J.S.T	-
	YC-931R		

(unit : mm)

MODEL NAME	CUT35/B
TDK-Lambda	

CA837-02-01/B-C