



CONNECTORS USED :

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (INPUT SIDE CN1)	B3P5-VH(LF)(SN)	J.S.T	1
PIN HEADER (OUTPUT SIDE CN51)	B5P-VH(LF)(SN)	J.S.T	1

*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

MATCHING HOUSINGS (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
SOCKET HOUSING (CN1)	VHR-5N	J.S.T	1
SOCKET HOUSING (CN51)	VHR-5N	J.S.T	1

MATCHING PINS & TOOL (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
TERMINAL PINS	SVH-21T-P1.1	J.S.T	8
	BVH-21T-P1.1		
HAND CRIMPING TOOL	YC-160R	J.S.T	-

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
TERMINAL PINS	SVH-41T-P1.1	J.S.T	8
	BVH-41T-P1.1		
HAND CRIMPING TOOL	YC-930R	J.S.T	-
	YC-931R		

NOTES :

- A: 4- ϕ 3.5 HOLES ARE CUSTOMER'S CHASSIS MOUNTING HOLES AND INSERT SPACER (MAX ϕ 6.2) OF HEIGHT OVER 8mm TO LIFT THE UNIT. ALL MUST BE SCREWED AND GROUNDED.
- B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, NOMINAL OUTPUT CURRENT, PEAK OUTPUT CURRENT AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS)ARE SHOWN ON THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS. COUNTRY OF MANUFACTURE WILL BE SHOWN ON THE NAME PLATE.
- C: \perp IS FOR SAFETY GROUND CONNECTION.
- D: TO KEEP THE DISTANCE MORE THAN 4mm BETWEEN PC-BOARD EDGE AND CUSTOMER CHASSIS.

(unit : mm)

MODEL NAME	CUT35J
TDK-Lambda	

CA873-02-01A