



CONNECTOR USED :

| PART DESCRIPTION | PART NAME | MANUFACTURER | QTY |
|------------------------------|-----------|--------------|-----|
| PIN HEADER (INPUT SIDE CN1) | B3P5-VH | JST | 1 |
| PIN HEADER (OUTPUT SIDE CN2) | B8P-VH | JST | 1 |
| PIN HEADER (OUTPUT SIDE CN3) | B2B-XH-A | JST | 1 |

* CURRENT OF THE CN2 CONNECTOR PIN MUST BE LESS THAN 5A (7A AT PEAK LOAD)

RECOMMENDED HOUSING & TERMINAL PIN :

* NOT INCLUDED WITH THE PRODUCT.

| PART DESCRIPTION | PART NAME | MANUFACTURER | QTY |
|--------------------------|-----------------------------------|--------------|-----|
| SOCKET HOUSING (CN1) | VHR-5N | JST | 1 |
| SOCKET HOUSING (CN2) | VHR-8N | JST | 1 |
| SOCKET HOUSING (CN3)*1 | XHP-2 | JST | 1 |
| TERMINAL PINS (CN1, CN2) | SVH-21T-P1.1 | JST | 11 |
| TERMINAL PINS (CN3)*1 | BXH-001T-P0.6 OR SXH-001T-P0.6 | JST | 2 |

HAND CRIMPING TOOL : YC-160R CN1,CN2 MANUFACTURER : JST
HAND CRIMPING TOOL : YC-110R OR YRS-110 CN3 MANUFACTURER : JST

*1 APPLICABLE ONLY WHEN USING REMOTE ON/OFF

== NOTE ==

- A. M4 EMBOSSED TAPPED & COUNTERSUNK HOLES (6) ARE FOR CUSTOMER'S CHASSIS MOUNTING. SCREW MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 6mm.
- B. ϕ 4.5 HOLES (3) AND R2.25 SLOT HOLES (2) ARE FOR CUSTOMER'S CHASSIS MOUNTING. (USE M4 MOUNTING SCREW)
- C. MODEL NAME, INPUT VOLTAGE RANGE, AVERAGE OUTPUT POWER, NOMINAL OUTPUT VOLTAGE, AVERAGE OUTPUT CURRENT, PEAK OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

- D. FG IS PROTECTIVE BONDING TERMINAL.
- E. CN3 IS NORMALLY SHORTED BY JM-2W-96(JST). IF USING REMOTE ON/OFF, REMOVE JM-2W-96 AND REFER TO THE TABLE FOR RECOMMENDED HOUSING AND TERMINAL PIN.

(unit : mm)

| | |
|-------------------|--------------|
| MODEL NAME | ZWD150PAF/JA |
| TDK-Lambda | |

PA573-02-01/JA-F