

CONNECTORS USED:


PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (INPUT SIDE CN1)	B3P-5-VH	J.S.T	1
PIN HEADER (OUTPUT SIDE CN51)	B8P-VH	J.S.T	1

*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

MATCHING HOUSINGS & PINS (NOT INCLUDED WITH PRODUCT):

SOCKET HOUSING (CN1)	VHR-5N	J.S.T	1
SOCKET HOUSING (CN51)	VHR-8N	J.S.T	1
TERMINAL PINS (CN1,51)	SVH-21T-P1.1	J.S.T	11

HAND CRIMPING TOOL : YC-160R MANUFACTURER : J.S.T



NOTES

- A : $4-\phi 3.5$ HOLES ARE CUSTOMER'S CHASSIS

- E : FG IS FOR SAFETY GROUND CONNECTION.

MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.

B : MODEL NAME, NOMINAL OUTPUT VOLTAGE, AVERAGE OUTPUT CURRENT AND PEAK OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

C : COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.

D : TO KEEP THE DISTANCE MORE THAN 2mm BETWEEN PC-BOARD EDGE AND CUSTOMER'S CHASSIS.

TDK-Lambda					
MODEL NAME	VS100P				
[]	(unit : mm)				