



= NOTES =

- A: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B: M4 EMBOSSED, TAPPED AND COUNTERSUNK HOLES (6) FOR CUSTOMER'S CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 6mm.
- C:  $\phi 4.5$  HOLES (6) FOR CUSTOMER'S CHASSIS MOUNTING. (USE M4 MOUNTING SCREW.)
- D: FG IS PROTECTIVE BONDING TERMINAL.
- E: CONNECTOR TO CHANGE V2,V3 OUTPUT VOLTAGE (CN71) : B4B-XH-AM (JST)  
 J61 SHORT : V2 OUTPUT VOLTAGE IS +12V.(\*)  
 J61 OPEN : V2 OUTPUT VOLTAGE IS +15V.  
 J71 SHORT : V3 OUTPUT VOLTAGE IS -12V.(\*)  
 J71 OPEN : V3 OUTPUT VOLTAGE IS -15V.

\*J61 AND J71 ARE NORMALLY SHORTED BY JM-2W-96(JST).  
 CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	B3P-5-VH	JST	1
PIN HEADER (OUTPUT SIDE CN51)	B8P-VH	JST	1
PIN HEADER (OUTPUT SIDE CN61)	B3P-VH	JST	1
PIN HEADER (OUTPUT SIDE CN81)	B6P-VH	JST	1

\*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

MATCHING HOUSINGS & PINS (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
SOCKET HOUSING (CN1)	VHR-5N	JST	1
SOCKET HOUSING (CN51)	VHR-8N	JST	1
SOCKET HOUSING (CN61)	VHR-3N	JST	1
SOCKET HOUSING (CN81)	VHR-6N	JST	1
TERMINAL PINS (CN1,51,61,81)	SVH-21T-P1.1	JST	20

HAND CRIMPING TOOL : YC-160R MANUFACT. : JST