


**NOTES**

- A: 4- $\phi$ 3.5 HOLES ARE FOR CUSTOMER'S CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.
- B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C:  $\perp$  IS PROTECTIVE BONDING TERMINAL.
- D: TO KEEP THE DISTANCE MORE THAN 4mm BETWEEN PCB EDGE AND CUSTOMER'S CHASSIS.

- E: OUTPUT TERMINAL INFORMATION (CN51)
  - \* OUTPUT TYPE 12V/15V : TERMINAL 1
  - \* OUTPUT TYPE 24V/36V/48V : TERMINAL 2



(unit : mm)

MODEL NAME	ZWS300BAF/T
<b>TDK-Lambda</b>	

A254-02-01/T-D