

## 100-150W AC-DC External Power Supplies

<https://product.tdk.com/en/power/dt-d>  
<https://www.emea.lambda.tdk.com/dt150>



Industrial



Broadcast



Test




COMM

Ranging from 100 to 150W, these DT100/150-D external power supplies are certified to UL/CSA/EN/IEC62368-1 and comply with DoE Level VI Efficiency. In addition to satisfying Energy Efficiency Level VI with an average efficiency of greater than 89% and an off-load power draw of less than 150mW, the products also meet EU Tier 2 requirements. All units meet EN55032-B, FCC Class B conducted & radiated emissions and EN55024 immunity standards.

Features	Benefits
• EU CoC Tier 2 & DoE Level VI Compliant	• Meets US and EU Energy Saving Legislation
• Wide Range AC Input (90-264VAC)	• Global Operation
• >89% Average Efficiency	• Consumes Less Energy
• Rugged Non-Vented Enclosure	• Suitable for Harsh Industrial Environment
• Alternative Connectors and Cable Assemblies	• Flexible System Integration

Model Selector						
Model	Output Voltage (V)	Maximum Current (A)	Maximum Power (W)	Oversvoltage Protection (V)	Output Regulation (%)	Ripple & Noise (mVpk-pk)
DT100PW120D	12	8.34	100	13.2 - 15.6	±5	240
DT100PW160D	16	6.25	100	17.6 - 20.8	±5	320
DT100PW190D	19	5.27	100	20.9 - 24.7	±5	380
DT100PW240D	24	4.17	100	26.4 - 31.2	±3	480
DT100PW360D	36	2.78	100	39.6 - 46.8	±3	480
DT100PW480D	48	2.09	100	52.8 - 62.4	±3	480
DT150PW120D	12	11.67	140	13.2 - 15.6	±5	240
DT150PW160D	16	9.38	150	17.6 - 20.8	±5	320
DT150PW190D	19	7.90	150	20.9 - 24.7	±5	380
DT150PW240D	24	6.25	150	26.4 - 31.2	±3	480
DT150PW360D	36	4.17	150	39.6 - 46.8	±3	480
DT150PW480D	48	3.13	150	52.8 - 62.4	±3	480



Specifications		
Model		DT100/150-D
<b>Input</b>		
Input Voltage range	Vac	90 - 264
Input Frequency	Hz	47 - 63
Input Current (90Vac)	A	2.5
Inrush Current at 230Vac (Cold Start)	A	<150 (25°C ambient)
Leakage Current (264Vac 60Hz)	uA	<600
Power Factor	-	Typically 0.9 at full load, 230VAC (Meets EN61000-3-2)
No Load Power Consumption	mW	<150
Hold Up Time (typ) at 115Vac Input	ms	16
Efficiency	%	>89 Avg. Active Efficiency (1)
Conducted & Radiated EMI	-	EN55032-B, FCC Part 15 Class B
Immunity	-	EN55024
Safety Agency Certifications	-	UL/CSA/EN/IEC62368-1, UL/CSA/EN/IEC60950-1, CE Mark (LVD, EMC and RoHS)
<b>Output</b>		
Voltage Accuracy	%	±1
Output Voltage Adjustment	-	None
Switching Frequency (Full Load)	kHz	45 - 55
Total Regulation	-	See Model Selector Table
Ripple & Noise (2)	-	See Model Selector Table
Temperature Coefficient	%/°C	±0.05
Minimum Load	-	No minimum load required
Overcurrent Protection	%	110 - 160 (Auto-Recovery)
Overvoltage Protection	-	See Model Selector Table (Cycle input power to reset)
Short Circuit Protection	-	Continuous - Hiccup Mode (Auto Recovery)
Parallel Operation	-	Not possible
<b>Environmental</b>		
Operating Temperature	°C	-20 to +60, de-rate linearly to 50% load from 40 to 60
Storage Temperature	°C	-20 to +85
Humidity (non condensing)	%RH	20 - 90
Cooling	-	Convection
Altitude	m	2,000
Withstand Voltage (For 1 minute)	Vac	Input to Ground 1,500, Input to Output 3,000, Output to Ground 500VDC (3)
IP Rating	-	IPX0
Vibration (non-operating)	m/s <sup>2</sup>	23.52 (10 - 55Hz: constant sweep 1 min X, Y, Z for 1 hour)
Shock	m/s <sup>2</sup>	<196.1 (20G)
<b>Other</b>		
Weight (Typ)	g	780
Size (LxWxH)	mm	170 x 85 x 44
Size (LxWxH)	Inches	6.70 x 3.35 x 1.73
AC Input Connector	-	IEC 320-C14 (Accepts IEC 320-C13)
DC Output Connector	-	Kycon KPPx-4P or equivalent Pins 1 & 2: -Vout, Pins 3 & 4: +Vout
Cable Length & Thickness	-	1050mm; 12 to 16V Models: UL2464 #16 AWG, 19 to 48V Models: UL2464 #18 AWG
MTBF (MIL-HNBK, 100% load, 25°C)	hrs	140,000
Warranty	yrs	3

## Notes


See website for detailed specifications, test methods and installation manual

(1) Measured at 25%, 50%, 75% and 100% load conditions

(2) Ripple and noise is measured at 20MHz BW. Add 0.1uF ceramic capacitor and 10uF Electrolytic capacitor in parallel across the output

(3) Versions available for output to be internally connected to ground. Contact local sales office.

**Outline Drawing**





**TDK-Lambda France SAS**

Tel: +33 1 60 12 71 65  
france@fr.tdk-lambda.com  
www.emea.lambda.tdk.com/fr



**Italy Sales Office**

Tel: +39 02 61 29 38 63  
info.italia@it.tdk-lambda.com  
www.emea.lambda.tdk.com/it



**Netherlands**

info@nl.tdk-lambda.com  
www.emea.lambda.tdk.com/nl



**TDK-Lambda Germany GmbH**

Tel: +49 7841 666 0  
info.germany@de.tdk-lambda.com  
www.emea.lambda.tdk.com/de



**Austria Sales Office**

Tel: +43 2256 655 84  
info@at.tdk-lambda.com  
www.emea.lambda.tdk.com/at



**Switzerland Sales Office**

Tel: +41 44 850 53 53  
info@ch.tdk-lambda.com  
www.emea.lambda.tdk.com/ch



**Nordic Sales Office**

Tel: +45 8853 8086  
info@dk.tdk-lambda.com  
www.emea.lambda.tdk.com/dk



**TDK-Lambda UK Ltd.**

Tel: +44 (0) 12 71 85 66 66  
info@uk.tdk-lambda.com  
www.emea.lambda.tdk.com/uk



**TDK-Lambda Ltd.**

Tel: +9 723 902 4333  
info@tdk-lambda.co.il  
www.emea.lambda.tdk.com/il



**C.I.S.**

**Commercial Support:**

Tel: +7 (495) 665 2627

**Technical Support:**

Tel: +7 (812) 658 0463

info@tdk-lambda.ru

www.emea.lambda.tdk.com/ru



**TDK-Lambda Americas**

Tel: +1 800-LAMBDA-4 or 1-800-526-2324  
powersolutions@us.tdk-lambda.com  
www.us.lambda.tdk.com



**TDK Electronics do Brasil Ltda**

Tel: +55 11 3289-9599  
sales.br@tdk-electronics.tdk.com  
www.tdk-electronics.tdk.com/en



**TDK-Lambda Corporation**

Tel: +81-3-6778-1113  
www.jp.lambda.tdk.com



**TDK-Lambda (China) Electronics Co. Ltd.**

Tel: +86 21 6485-0777  
powersolutions@cn.tdk-lambda.com  
www.lambda.tdk.com.cn



**TDK-Lambda Singapore Pte Ltd.**

Tel: +65 6251 7211  
tts.mkt@sg.tdk-lambda.com  
www.sg.lambda.tdk.com



**TDK India Private Limited, Power Supply Division**

Tel: +91 80 4039-0660  
mathew.philip@in.tdk-lambda.com  
www.sg.lambda.tdk.com

