

Data Base : MIL - HDBK - 217F Notice 1

Environment : GB, 25°C

Input: 115V

Output: Full Load

Unit : KPSA10-15

Ver: V10

Date: 2008/7/1

CAT	TYPE	Q'ty		λp	$\lambda(\lambda p * Q'ty)$	%
5.1	Microcircuits	1	IC1	0.0332	0.0332	1.92
6.1	Diode, Fast	1	D3	0.0616	0.0616	3.55
6.1	Diode, Fast	1	D4	0.0205	0.0205	1.18
6.1	Diode,General	1	BR1	0.0011	0.0011	0.07
6.1	Diode,General	1	D1	0.0011	0.0011	0.07
6.1	Diode,General	1	D2	0.0011	0.0011	0.07
6.1	Voltage Regulator	1	IC3	0.0110	0.0110	0.63
6.1	Diode,Zener	1	ZD2	0.0110	0.0110	0.63
6.4	Transistor MOSFET	1	Q3	0.2640	0.2640	15.22
6.11	Optocoupler	1	IC2	0.0715	0.0715	4.12
6.11	Light Emitting Diode	1	LED1	0.0013	0.0013	0.07
9.2	Resistor film	1	R4	0.0036	0.0036	0.21
9.2	Resistor film	1	R5	0.0036	0.0036	0.21
9.2	Resistor film	1	R6	0.0036	0.0036	0.21
9.2	Resistor film	1	R7	0.0031	0.0031	0.18
9.2	Resistor film	1	R8	0.0031	0.0031	0.18
9.2	Resistor film	1	R9	0.0031	0.0031	0.18
9.2	Resistor film	1	R10	0.0074	0.0074	0.43
9.2	Resistor film	1	R11	0.0032	0.0032	0.19
9.2	Resistor film	1	R12	0.0032	0.0032	0.18
9.2	Resistor film	1	R13	0.0031	0.0031	0.18
9.2	Resistor film	1	R14	0.0031	0.0031	0.18
9.2	Resistor film	1	R15	0.0031	0.0031	0.18
9.2	Resistor film	1	R16	0.0031	0.0031	0.18
9.2	Resistor film	1	R18	0.0062	0.0062	0.36
9.2	Resistor film	1	R20	0.0032	0.0032	0.19
9.2	Resistor film	1	R21	0.0032	0.0032	0.18
9.2	Resistor film	1	ZD1	0.0031	0.0031	0.18
9.8	Resistor thermistor	1	TH1	0.0650	0.0650	3.75
9.9	Resistor Variable	1	VR1	0.1328	0.1328	7.65
10.5	Capacitor metallized	1	Z1	0.0288	0.0288	1.66
10.1	Capacitor ceramic	1	C3	0.0056	0.0056	0.32
10.1	Capacitor ceramic	1	C4	0.0056	0.0056	0.32
10.1	Capacitor ceramic	1	C5	0.0102	0.0102	0.59
10.1	Capacitor ceramic	1	C7	0.0067	0.0067	0.38
10.1	Capacitor ceramic	1	C11	0.0089	0.0089	0.51
10.1	Capacitor ceramic	1	CX1	0.0342	0.0342	1.97
10.1	Capacitor ceramic	2	CY1,CY2	0.0062	0.0123	0.71
10.14	Capacitor electrolytic	1	C1	0.0767	0.0767	4.42

Data Base : MIL - HDBK - 217F Notice 1

Environment : GB, 25°C

Input: 115V

Output: Full Load

Unit : KPSA10-15

Ver: V10

Date: 2008/7/1

CAT	TYPE	Q'ty		λ_p	$\lambda(\lambda_p*Q'ty)$	%
10.14	Capacitor electrolytic	1	C2	0.1021	0.1021	5.89
10.14	Capacitor electrolytic	1	C8	0.2931	0.2931	16.90
10.14	Capacitor electrolytic	1	C9	0.2931	0.2931	16.90
11.1	Transformer	1	T1	0.0661	0.0661	3.81
11.2	Inductive	3	L1,L2,R1	0.0084	0.0251	1.45
22.1	Fuses	1	F1	0.0100	0.0100	0.58
16.1	Circuit Board	1	PCB	0.0005	0.0005	0.03
17.1	Joint hand soldered	4	Pin	0.0003	0.0011	0.06
17.1	Joint machine soldered	121		0.0001	0.0167	0.96
Component Count =		53		Total FR =	1.7344	
				MTBF =	576,555	Hours
				MTBF=(1/Failure Rate (FR))*10 ⁶ Hours		