

Data Base : MIL - HDBK - 217F Notice 1

Environment : GB, 25°C

Input: 115V

Output: Full Load

Unit : ZPSA40-24

Ver: V10

Date: 2008/8/21

CAT	TYPE	Q'ty		$\lambda p$	$\lambda (\lambda p * Q'ty)$	%
5.1	Microcircuits	1	IC3	0.033	0.033	1.16
6.1	Diode, Fast	1	D1	0.020	0.020	0.72
6.1	Diode, Fast	1	D2	0.020	0.020	0.72
6.1	Diode,General	1	BR1	0.001	0.001	0.04
6.1	Diode,General	1	D3	0.001	0.001	0.04
6.1	Diode, Schottky	2	D4,D5	0.002	0.005	0.17
6.1	Voltage Regulator	2	IC2,IC4	0.011	0.022	0.77
6.1	Diode,Zener	4	ZD1,ZD2,ZD3	0.011	0.044	1.54
6.4	Transistor MOSFET	1	Q1	0.264	0.264	9.24
6.11	Optocupler	1	IC1	0.072	0.072	2.50
6.11	Light Emitting Diode	1	LED	0.001	0.001	0.04
9.1	Resistor fixed	1	R1	0.001	0.001	0.03
9.1	Resistor fixed	1	R4	0.001	0.001	0.04
9.1	Resistor fixed	2	J1,J2	0.001	0.002	0.05
9.2	Resistor film	2	R2,R3	0.005	0.010	0.36
9.2	Resistor film	1	R6	0.003	0.003	0.12
9.2	Resistor film	1	R7	0.003	0.003	0.12
9.2	Resistor film	2	R9,R10	0.005	0.010	0.36
9.2	Resistor film	1	R11	0.004	0.004	0.13
9.2	Resistor film	1	R12	0.004	0.004	0.13
9.2	Resistor film	1	R13	0.003	0.003	0.11
9.2	Resistor film	1	R14	0.004	0.004	0.13
9.2	Resistor film	1	R15	0.003	0.003	0.11
9.2	Resistor film	1	R16	0.003	0.003	0.11
9.2	Resistor film	1	R17	0.003	0.003	0.11
9.2	Resistor film	1	R18	0.003	0.003	0.11
9.2	Resistor film	1	R20	0.003	0.003	0.11
9.2	Resistor film	1	R21	0.003	0.003	0.11
9.2	Resistor film	1	R22	0.003	0.003	0.12
9.2	Resistor film	1	R23	0.003	0.003	0.12
9.2	Resistor film	1	R24	0.003	0.003	0.11
9.2	Resistor film	2	R27,R27A	0.005	0.010	0.34
9.8	Resistor thermistor	1	TH1	0.065	0.065	2.27
9.9	Resistor Variable	1	VR1	0.133	0.133	4.65
10.5	Capacitor metallized	1	Z1	0.017	0.017	0.60
10.1	Capacitor ceramic	1	C1	0.006	0.006	0.22

Data Base : MIL - HDBK - 217F Notice 1

Environment : GB, 25°C

Input: 115V

Output: Full Load

Unit : ZPSA40-24

Ver: V10

Date: 2008/8/21

CAT	TYPE	Q'ty		$\lambda p$	$\lambda (\lambda p * Q'ty)$	%
10.1	Capacitor ceramic	1	C2	0.012	0.012	0.41
10.1	Capacitor ceramic	1	C6A	0.014	0.014	0.48
10.1	Capacitor ceramic	1	C8	0.004	0.004	0.15
10.1	Capacitor ceramic	1	C11	0.008	0.008	0.27
10.1	Capacitor ceramic	1	C13	0.004	0.004	0.15
10.1	Capacitor ceramic	1	C14	0.006	0.006	0.20
10.1	Capacitor ceramic	1	C16	0.012	0.012	0.42
10.1	Capacitor ceramic	1	CX1	0.034	0.034	1.18
10.1	Capacitor ceramic	3	CY1,CY2,CY3	0.030	0.091	3.19
10.14	Capacitor electrolytic	4	C3,C4,C5,C7	0.385	1.538	53.83
10.14	Capacitor electrolytic	1	C6	0.143	0.143	5.02
10.14	Capacitor electrolytic	1	C9	0.087	0.087	3.04
11.1	Transformer	1	T1	0.066	0.066	2.31
11.2	Inductive	2	L1,L2	0.008	0.017	0.59
22.1	Fuses	1	F1	0.010	0.010	0.35
16.1	Circuit Board	1	PCB	0.001	0.001	0.02
17.1	Joint hand soldered	2	CON1,CON2	0.000	0.001	0.02
17.1	Joint machine soldered	162		0.000	0.022	0.78
Component Count =		69		Total FR =	2.8574	
				MTBF =	349,964	Hours
					MTBF=(1/Total FR)*10 <sup>6</sup> Hours	