

Data Base : MIL - HDBK - 217F Notice 1

Environment : GB, 25°C

Input: 115V

Output: Full Load

Unit : ZPSA60-12

Ver: V11

Date: 2008/8/21

CAT	TYPE	Q'ty		λp	$\lambda (\lambda p * Q'ty)$	%
5.1	Microcircuits	1	IC3	0.033	0.033	1.52
6.1	Diode, Fast	1	D1	0.020	0.020	0.94
6.1	Diode,General	1	BR1	0.001	0.001	0.05
6.1	Diode,General	1	D2	0.001	0.001	0.05
6.1	Diode,General	1	D3	0.001	0.001	0.05
6.1	Diode, Schottky	2	D4,D5	0.002	0.004	0.16
6.1	Voltage Regulator	1	IC2	0.011	0.011	0.50
6.1	Diode,Zener	3	ZD1,ZD3,ZD4	0.011	0.033	1.51
6.4	Transistor MOSFET	1	Q1	0.264	0.264	12.10
6.11	Optocoupler	1	IC1	0.072	0.072	3.28
6.11	Light Emitting Diode	1	LED	0.001	0.001	0.06
9.1	Resistor fixed	1	R1	0.001	0.001	0.03
9.1	Resistor fixed	1	R4	0.002	0.002	0.07
9.1	Resistor fixed	2	J1,J2	0.001	0.002	0.07
9.2	Resistor film	2	R2,R3	0.005	0.010	0.47
9.2	Resistor film	2	R9,R10	0.005	0.010	0.47
9.2	Resistor film	1	R11	0.004	0.004	0.17
9.2	Resistor film	1	R12	0.004	0.004	0.17
9.2	Resistor film	1	R13	0.003	0.003	0.14
9.2	Resistor film	1	R14	0.003	0.003	0.15
9.2	Resistor film	1	R15	0.003	0.003	0.14
9.2	Resistor film	1	R16	0.003	0.003	0.14
9.2	Resistor film	1	R17	0.003	0.003	0.15
9.2	Resistor film	1	R18	0.003	0.003	0.14
9.2	Resistor film	1	R20	0.003	0.003	0.14
9.2	Resistor film	1	R21	0.003	0.003	0.15
9.2	Resistor film	1	R22	0.005	0.005	0.21
9.2	Resistor film	1	R23	0.004	0.004	0.17
9.2	Resistor film	1	R24	0.003	0.003	0.14
9.2	Resistor film	2	R27,R27A	0.003	0.007	0.31
9.2	Resistor film	1	ZD2	0.003	0.003	0.14
9.8	Resistor thermistor	1	TH1	0.065	0.065	2.98
9.9	Resistor Variable	1	VR1	0.133	0.133	6.09
10.5	Capacitor metallized	1	Z1	0.017	0.017	0.79
10.1	Capacitor ceramic	1	C1	0.006	0.006	0.26
10.1	Capacitor ceramic	1	C2	0.006	0.006	0.28

Data Base : MIL - HDBK - 217F Notice 1

Environment : GB, 25°C

Input: 115V

Output: Full Load

Unit : ZPSA60-12

Ver: V11

Date: 2008/8/21

CAT	TYPE	Q'ty		λp	$\lambda (\lambda p * Q'ty)$	%
10.1	Capacitor ceramic	1	C6A	0.014	0.014	0.63
10.1	Capacitor ceramic	1	C10	0.006	0.006	0.26
10.1	Capacitor ceramic	1	C11	0.009	0.009	0.39
10.1	Capacitor ceramic	1	C12	0.006	0.006	0.25
10.1	Capacitor ceramic	1	C13	0.004	0.004	0.20
10.1	Capacitor ceramic	1	C14	0.006	0.006	0.26
10.1	Capacitor ceramic	1	C15	0.061	0.061	2.78
10.1	Capacitor ceramic	1	CX1	0.034	0.034	1.55
10.1	Capacitor ceramic	3	CY1,CY2,CY3	0.030	0.091	4.17
10.14	Capacitor electrolytic	4	C3,C4,C5,C7	0.218	0.871	39.94
10.14	Capacitor electrolytic	1	C6	0.154	0.154	7.07
10.14	Capacitor electrolytic	1	C9	0.065	0.065	2.96
11.1	Transformer	1	T1	0.066	0.066	3.03
11.2	Inductive	2	L1,L2	0.008	0.017	0.77
22.1	Fuses	1	F1	0.010	0.010	0.46
16.1	Circuit Board	1	PCB	0.001	0.001	0.02
17.1	Joint hand soldered	2	CON1,CON2	0.000	0.001	0.03
17.1	Joint machine soldered	157		0.000	0.022	0.99
Component Count =		67		Total FR =	2.1814	
				MTBF =	458,416	Hours
					MTBF=(1/Total FR)*10 ⁶ Hours	